



SD-120H



Simple Operation

Simple operation by time switch (0-30min.)

Strong Durability

Waterproof by silicon, strong stainless body

Strong Cleaning performance

Built in powerful BLT vibrator

Warming up mode


Keep up the temperature of liquid (65c).

Specification

Model	SD-120H	Consumption Wattage	0.65A
Inside Diameter	150(W)×135(L)×100(H)	Gross Weight	2.7 KG
Outside Diameter	177(W)×162(L)×211(H)	Power	AC220V / 60Hz
Capacity	1.8L	Operation Time	0-30min. heat-on temp. 65°C ±10%
Ultrasonic Frequency	40KHz	Materials	tub:SUS-304 body:SUS-430
Ultrasonic Output	50W	Parts	cover, fuse x 2, manual

Cleaning Liquid & Spare parts (for option)

Required for better cleaning performance

Cleaning Liquid			BASKET	
Model	11UN	16PLUS	BT-120	
Component	Alkali	Neutrality		
Target	glass,quartz,ceramic ware,crystal compound,rubber, iron, metal	aluminum,zinc,tin,borosilicate, glass, quartz glass, stainless,chrome, nickel, polyethylene polypropylene, Teflon, silicon rubber, rubber		nonferrous metal, stainless,chrome steel, iron steel,precious metal, titanium, nickel
Solution rate	3/100%	3/100%		3/100%

SD-ULTRASONIC CO.,LTD

No.560, Sewoon B/D, #173 Jangsa-dong, Jongro-ku, Seoul, Korea
Tel] +82-1644-5897 Fax] +82-2-2278-2276
<http://www.sd-ultra.com>